

## FITTING INSTRUCTIONS

### RicClip®

It is recommended that the RicClip be initially fitted immediately after a routine maintenance check of the vehicle.

The vehicle's wheels should have been removed and inspected for any wear or damage along with nuts, studs, and wheel hubs e.g. by using a Checkthread Kit\*. Any worn or damaged components should be replaced. The nuts and studs should be clean and lightly lubricated.

After refitting the wheels, the wheel nuts should be tightened to the correct torque as recommended by the vehicle manufacturer and RicClips should be fitted.

After the vehicle has completed approximately 50km, the RicClips should be removed and the wheel nuts re-tightened to the correct torque. If there is significant movement of the nuts during this exercise the check should be repeated after a further 50km.

The wheel torque should then be further checked after 1 week, following which the assembly should remain secure for the remainder of the maintenance period. But, if at any check there has been a noticeable reduction in the recommended torque, a repeat check should be made after 50km.


Select the correct RicClip for the application. RicClips are designed in various lengths to fit specific sized nuts and to suit both left and right hand thread applications.

After selecting the correct RicClip for the application, fit using RicClip fitting tools or by hand as follows:


Pull the locking arms outwards and rest the hooked ends on the central bar. Push the RicClip over two adjacent nuts, holding the locking arms out if necessary.

Release the locking arms from their resting position and hook them over each other by hand or by using the fitting tool.

\*Checkthread Kits please enquire.



Hold the RicClip at points 'A' and 'B'. Open the locking arms by pulling in the direction of arrows.



Ensuring that the plastic tag and the hook ends are facing the wheel, push the RicClip over two adjacent nuts until it is 5 to 8mm from the wheel face.



Hook locking arms over each other by hand or with fitting tool.

PL REF	DESCRIPTION	COLOUR CODE
PL29933	RIC-CLIP 24MM RH	SILVER
PL29934	RIC-CLIP 27MM RH	BLACK
PL29935	RIC-CLIP 30MM RH	YELLOW
PL29936	RIC-CLIP 32MM RH	SILVER
PL29937	RIC-CLIP 33MM RH	BLUE
PL29938	RIC-CLIP APPLICATOR	N/A